

# Flotrex\* PN

## pleated filters with polypropylene microfiber media



**Figure 1: Flotrex PN Filters**

### description and use

The Flotrex PN (FPN) microfiber filters (Figure 1) offer an economical solution for your filtration needs. The all polypropylene construction of the FPN filters provides superior chemical compatibility. The gradient density, thermally bonded polypropylene media has excellent dirt holding capacities and reliable retention characteristics. FPN filters do not contain any adhesives or additives.

### typical applications

FPN filters are an economical alternative to membrane filters in a broad range of applications, including:

- Filtration of liquid polymers, coatings, and inks
- Filtration of bulk chemicals
- Beer trap filtration
- Post Carbon bed and DI bed filtration
- Pre-filtration to protect expensive final filters

### general properties

Flotrex PN filters are available in the following nominal pore size micron rating: 0.2 0.45, 1, 2, 3, 5, 10

Find a contact near you by visiting [www.suezwatertechnologies.com](http://www.suezwatertechnologies.com) and clicking on "Contact Us".

\*Trademark of SUEZ; may be registered in one or more countries.

©2017 SUEZ. All rights reserved.

and 30 µm. Tables 1, 2, 3, and 4 show further details on materials of construction, dimensions, operational limits, and flow performance.

**Table 1: Materials of Construction**

Description	Material of Construction
Filtration Media	Polypropylene Microfiber
Support Layers	Polypropylene Microfiber
Core and Cage	Polypropylene
Endcaps and Adapters	Polypropylene

**Table 2: Dimensions**

Filter Model	Nominal O.D.	Nominal I.D.	Effective Filtration Area
FPN92	2.75" (70 mm)	1.25" (31mm)	4.8 ft <sup>2</sup> (0.45m <sup>2</sup> )
FPN94	2.75" (70 mm)	1.25" (31mm)	5.5 ft <sup>2</sup> (0.51m <sup>2</sup> )
FPN03, FPN05	2.75" (70 mm)	1.25" (31mm)	5.5 ft <sup>2</sup> (0.51m <sup>2</sup> )
FPN01, FPN02	2.75" (70 mm)	1.25" (31mm)	6.4 ft <sup>2</sup> (0.59m <sup>2</sup> )
FPN10, FPN30	2.75" (70 mm)	1.25" (31mm)	7.3 ft <sup>2</sup> (0.68m <sup>2</sup> )


**Table 3: Operational Limits**

Description	Operational Limits
Maximum Forward Differential Pressure	60 psi (4.1 bar) at 70°F (21°C)
Maximum Reverse Differential Pressure	30 psi (2.1 bar) at 70°F (21°C)
Maximum Operating Temperature	180°F (82°C) at 10 psid (0.69 bar) in water

## additional information

- Flotrex PN filters may be autoclaved or in situ steam sterilized (up to 257°F [125°C], 30-minute cycles) for a maximum accumulated exposure of 10 hours. Alternately, the filters may be sanitized with compatible chemical agents.
- SUEZ certifies that the material contained in its Flotrex PN pleated filters meet U.S. FDA requirements for food contact under the applicable regulations in 21 CFR. For further information, contact SUEZ technical services. Flotrex PN filters meet the test criteria for USP class VI-121°C Plastics.
- Aqueous extracts from Flotrex PN filters contain less than 0.25 EU/ml. The filters typically exhibit low levels of non-volatile residues.
- SUEZ filter cartridges are designed and manufactured for resistance to a wide range of chemical solutions. Conditions will vary with each application and users should carefully verify chemical compatibility. Please contact your SUEZ distributor for more information.
- Table 5 provides additional ordering information.

**Table 4: Flow Performance in Clean Water<sup>1</sup>**



<sup>1</sup>Data based on 10" length filter

**Table 5: Ordering Information**

Type	Nominal Micron Rating	Nominal Cartridge Length	End #1 Adapter	End #2 Adapter	Elastomer Material
FPN	92 = 0.2 µm	1 = 10 inch (25 cm)	A = Open End	A = Open End Gasket	B = Buna-N
	94 = 0.45 µm	2 = 20 inch (51 cm)	Gasket	B = 120 O-Ring	E = EPDM
	01 = 1.0 µm	3 = 30 inch (76 cm)	B = 120 O-Ring	C = 213 O-Ring	S = Silicone
	02 = 2.0 µm	4 = 40 inch (102 cm)	C = 213 O-Ring	G = Closed End Cap	T = Teflon <sup>3</sup>
	03 = 3.0 µm		E = 222 O-Ring	H = Fin Adapter	V = Viton <sup>3</sup>
	05 = 5.0 µm		F = 226 O-Ring		
	10 = 10.0 µm		J = 020 O-Ring		
	30 = 30,0 µm		Q = 222 O-Ring		
	<b>Example:</b>		Stainless Steel		
	<b>FPN921AAE</b>		Insert <sup>2</sup>		
			Z = 226 O-Ring		
			Stainless Steel		
			Insert <sup>2</sup>		

<sup>2</sup>Q or Z Adapters normally require G or H adapters

<sup>3</sup>Teflon and Viton are registered trademarks of DuPont

